



10152245

## Frame 5gang, R.3, black glossy

### Technical properties

#### Dimensions

Depth	9.9 mm
Height	364.7 mm
Width	80.75 mm

#### Capacity

Number of sockets	5
-------------------	---

#### Materials

Colour of labelling	217,217,217
Colour of design line	black
Material for printing	PC-PMA black
Surface appearance	glossy
Material / surface	metal, aluminum profile
Type of surface treatment	untreated

#### Installation, mounting

Installation mode	for vertical and horizontal mounting ; clamp fastening
-------------------	--

#### Settings

Shading parameter	R1_czarny
Laser parameter	R1_schwarz

#### Equipment

Type of configuration	Laserdruck
-----------------------	------------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Identification

Main design line	Berker R.3
------------------	------------

#### Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---