



10156096

**Frame 5gang, Q.3, ant. velvety, lacq.**

**Technical properties**

**Dimensions**

|        |          |
|--------|----------|
| Depth  | 9.9 mm   |
| Height | 80.7 mm  |
| Width  | 364.5 mm |

**Capacity**

|                   |   |
|-------------------|---|
| Number of sockets | 5 |
|-------------------|---|

**Materials**

|                        |                         |
|------------------------|-------------------------|
| Colour of design line  | anthracite              |
| Material / workmanship | lacquered               |
| Surface appearance     | velvety                 |
| Material / surface     | metal, aluminum profile |

**Installation, mounting**

|                   |  |
|-------------------|--|
| Installation mode | for vertical and horizontal mounting ; clamp fastening |
|-------------------|--|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |
| Halogen free  | Yes |

**Identification**

|                  |            |
|------------------|------------|
| Main design line | Berker Q.3 |
|------------------|------------|

**Instructions**

|                   |   |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|