



10156099

Frame 5gang, Q.3, p. white velvety

Technical properties

Dimensions

| | |
|--------|----------|
| Depth | 9.9 mm |
| Height | 80.7 mm |
| Width | 364.5 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 5 |
|-------------------|---|

Materials

| | |
|---------------------------|-------------------------|
| Colour of design line | polar white |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Surface appearance | velvety |
| Material / surface | metal, aluminum profile |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|-------------------|--|
| Installation mode | for vertical and horizontal mounting ; clamp fastening |
|-------------------|--|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |

Identification

| | |
|------------------|------------|
| Main design line | Berker Q.3 |
|------------------|------------|

Instructions

| | |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|