



10437009

Surface-mtd housing 3gang, K.1, p. white glossy

Technical properties

Dimensions

| | |
|-----------------|---------|
| Depth | 41.5 mm |
| Insertion depth | 36 mm |

Materials

| | |
|-----------------------|-----------------------|
| Colour of design line | polar white |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Surface appearance | glossy |

Installation, mounting

| | |
|-------------------|--|
| Entries | entry at top, below and at each side in the middle possible |
| Installation mode | for mounting on combustible base surface ; for vertical mounting |

Cable

| | |
|------|--------------------------|
| Wire | with line and duct entry |
|------|--------------------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |

Identification

| | |
|------------------|------------|
| Main design line | Berker K.1 |
|------------------|------------|

Instructions

| | |
|------------------|---|
| Information text | For matching pipe lead-ins and replacement for cable and duct entries, refer to the chapter Dry surface-mounted installation. |
|------------------|---|