



10527009

**Surface-mtd housing 2gang hor., K.1, p. white glossy**

**Technical properties**

**Dimensions**

|                 |         |
|-----------------|---------|
| Depth           | 41.5 mm |
| Insertion depth | 36 mm   |

**Materials**

|                       |                       |
|-----------------------|-----------------------|
| Colour of design line | polar white           |
| Colour                | white                 |
| RAL colour            | RAL 9010 - Pure white |
| Surface appearance    | glossy                |

**Installation, mounting**

|                   |  |
|-------------------|--|
| Entries           | entry at top, below and at each side in the middle possible        |
| Installation mode | for mounting on combustible base surface ; for horizontal mounting |

**Cable**

|      |                          |
|------|--------------------------|
| Wire | with line and duct entry |
|------|--------------------------|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |
| Halogen free  | No  |

**Identification**

|                  |            |
|------------------|------------|
| Main design line | Berker K.1 |
|------------------|------------|

**Instructions**

|                  |   |
|------------------|---|
| Information text | For matching pipe lead-ins and replacement for cable and duct entries, refer to the chapter Dry surface-mounted installation. |
|------------------|---|