



1061

## Double pole socket outlet for floating output module inserts

### Technical properties

#### Dimensions

Insertion depth	17.5 mm
-----------------	---------

#### Materials

Material	Plastic/metal
Surface appearance	other

#### Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

#### Connection

Conductor cross-section (rigid)	6
Connection pins	according to DIN 42801
Type of connection	with screw terminals

#### Use

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

#### Identification

Application, usage	Connecting systems and accessories
Main design line	Accessories
Secondary design line(s)	ACCESSORIES, Berker Arsys, Berker B.3, Berker B.7, Berker S.1, wg-up ip 44