



1061

## Double pole socket outlet for floating output module inserts

### Technical properties

#### Dimensions

Insertion depth 17.5 mm

#### Materials

Surface appearance other

#### Installation, mounting

Installation mode without spreader claws

#### Connection

Conductor cross-section (rigid) max. 6 mm<sup>2</sup>

Connection pins according to DIN 42801

Type of connection with screw terminals

#### Use

Differentiation characteristic 3 - Sales with screw terminals

#### Safety

REACH conform Yes

RoHS conform Yes

#### Identification

Application, usage Connecting systems and accessories

Main design line Accessories

Secondary design line(s) ACCESSORIES ; Berker Arsys ; Berker B.3 ; Berker B.7 ; Berker S.1 ; wg-up ip 44