



**Frame 4gang hor., K.5, al., al. anodised**

**Technical properties**

**Dimensions**

|        |         |
|--------|---------|
| Depth  | 9.9 mm  |
| Height | 80.5 mm |
| Width  | 300 mm  |

**Capacity**

|                   |   |
|-------------------|---|
| Number of sockets | 4 |
|-------------------|---|

**Materials**

|                        |                     |
|------------------------|---------------------|
| Colour of design line  | Aluminium           |
| Material / workmanship | aluminium, anodised |
| Surface appearance     | matt                |

**Installation, mounting**

|                   |                 |
|-------------------|-----------------|
| Installation mode | clamp fastening |
|-------------------|-----------------|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |
| Halogen free  | Yes |

**Identification**

|                  |            |
|------------------|------------|
| Main design line | Berker K.5 |
|------------------|------------|

**Instructions**

|                   |   |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
|-------------------|---|

13837003