



1391

Glass cover plate 1gang TS polar white glossy

Technical properties

Dimensions

| | |
|--------------|--------|
| Depth | 5 mm |
| Screw length | 25 mm |
| Height | 160 mm |
| Width | 86 mm |

Materials

| | |
|-----------------------|--|
| Colour of design line | polar white |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Surface appearance | glossy |
| Material / surface | glass with polar white imprint on the rear |

Installation, mounting

| | |
|----------------------|--|
| Screws / screwdriver | each with 2 M3.5 x 25 mm two-hole screws in chrome, gold and stainless steel for dismantling protection ; with screwdriver |
| Installation mode | for vertical and horizontal mounting ; clamp fastening |

Equipment

| | |
|----------|-------------------------------|
| Subplate | with polar white plastic base |
|----------|-------------------------------|

Safety

| | |
|-----------------|------|
| Impact strength | IK02 |
|-----------------|------|

Identification

| | |
|------------------|-----------|
| Main design line | Berker TS |
|------------------|-----------|

Instructions

| | |
|------------------|---|
| Information text | Other components from the B.7 glass range are available, e.g. socket outlets. Observe scale drawings! |
|------------------|---|