



14321909

Central plate inst. opening Ø 22.5 mm, com-tech, p. white matt/velvety

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Dimensions

Screw spacing	36 mm
---------------	-------

Materials

Colour of design line	polar white
-----------------------	-------------

Surface appearance	matt/velvety
--------------------	--------------

Installation, mounting

Installation aperture	according to IEC 60947-5-1
-----------------------	----------------------------

Cut-out	with cut-out dia. 22.5 mm
---------	---------------------------

Installation mode	without spreader claws
-------------------	------------------------

Equipment

Supporting plate / Supporting ring	with supporting plate
------------------------------------	-----------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Impact strength	IK05
-----------------	------

Identification

Application, usage	Communication technology
--------------------	--------------------------

Main design line	Central plate system
------------------	----------------------

Secondary design line(s)	Communication technology ; Berker S.1 ; Berker B.3 ; Berker B.7 ; Berker Q.1 ; Berker Q.3
--------------------------	---

Instructions

Information text	For detailed information on relevant articles of other manufacturers, please see the Berker online catalogue.
------------------	---