



1687

LED unit for switches/push-buttons, light control, blue

Technical properties

Controls and indicators

Rocker switch/rocker push-button	for change-over/intermediate switch and on/off switch, 2-pole, 10 AX ; for rocker push-buttons and multiple rockers push-buttons, except order no. 503404, 503808
----------------------------------	---

Main electrical features

Rated voltage	12...48 V AC
Rated current	0.2...0.9 mA

Endurance

Service life of the LED	≈ 100000 h
-------------------------	------------

Materials

Colour independent of design lines	blue
------------------------------------	------

Equipment

Lighting	for lighting and monitoring circuit
Combination rocker switches/rocker push-buttons	for series switch illuminated

Use cases

Application	Light control
-------------	---------------

Safety

REACH conform	Yes
RoHS conform	Yes

Identification

Application, usage	Surface-mounted wet-room installation ; Light control
Main design line	Light control
Secondary design line(s)	Light control ; ACCESSORIES

Instructions

Special note text	Refer to the overview for the matching flush-mounted inserts. ; these marked articles (see symbol) are only suitable for the water-protected flush-mounted installation IP44 in conjunction with the corresponding seal, frame and contact protection box (imprint "IP44").
Information text	Connection to DC voltage within the specified voltage range, ensuring the correct polarity.