



181110

**Push-button, NO contact, TS, chrome glossy, brass galvanised**

**Technical properties**

**Architecture**

Type of control unit Push button

**Configuration**

Switch mode Normally open contact

Antibacterial treatment No

**Compatibility**

IFTTT support available No

**Main electrical features**

Nominal voltage 12 V

Rated voltage 12 V

**Electric current**

Momentary-contact current 1.5 A

**Dimensions**

Depth 19.7 mm

Insertion depth 13 mm

Height 22 mm

Width 22 mm

**Materials**

Colour of design line chrome

Material / workmanship brass galvanised

Surface appearance glossy

Material / surface brass, refined

**Installation, mounting**

Installation mode for screw fastening

**Connection**

Type of connection with plug-in terminals

**Scope of delivery**

With lamp No

**Equipment**

Quantity of NC contacts 1

Quantity of NO contacts 1

**Safety**

---

REACH conform Yes

RoHS conform Yes

**Use conditions**

---

Operating temperature -20...60 °C

**Identification**

---

Main design line Berker TS

**Instructions**

---

Special note text For connection via system interfaces to radio bus, KNX radio or KNX installations. Alternatively, can be used to control relay circuits.