



181112

Push-button, NO contact, TS, gold glossy, 24-carat galvanised

Technical properties

Architecture

Type of control unit	Push button
----------------------	-------------

Configuration

Switch mode	Normally open contact
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	12 V
Rated voltage	12 V

Electric current

Momentary-contact current	1.5 A
---------------------------	-------

Dimensions

Depth	19.7 mm
Insertion depth	13 mm
Height	22 mm
Width	22 mm

Materials

Colour of design line	gold
Colour	gold
Colour	gold optics
RAL colour	RAL 1004 - Golden yellow
Material	brass
Material / surface	brass, refined

Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

Connection

Type of connection	with plug-in terminals
--------------------	------------------------

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature -20...60 °C

Identification

Main design line Berker TS

Instructions

Special note text For connection via system interfaces to radio bus, KNX radio or KNX installations. Alternatively, can be used to control relay circuits.