



2041

Mechanical timer, 120 min, light control

Technical properties

Functions

Running time 120 mn

Configuration

Switch mode 2-pole off

Main electrical features

Rated voltage 250 V AC

Electric current

Switching current 16 AX

Dimensions

Insertion depth 32.3 mm

Materials

Material Plastic/metal

Installation, mounting

Installation mode without spreader claws

Connection

Terminal with through terminal

Type of connection with screw terminals

Settings

Setting reset with slip-clutch

Use cases

Application Light control

Identification

Application, usage Light control

Main design line Light control