



28808989

## Radio Touch, with loudspeaker, S.1/B.3/B.7, polar white glossy

### Technical properties

#### Functions

Function volume control, countdown, sleep timer, alarm clock with snooze function

#### Compatibility

For loudspeakers per channel 4...8 Ω

#### Controls and indicators

Operation operation via sensor areas of the touch display

Indication / display Time and date display, illuminated touch graphics display

#### Connectivity

Reception / transmission stereo FM radio with RDS display

Inputs external audio input AUX IN

#### Main electrical features

Frequency 50/60 Hz

#### Dimensions

Insertion depth 33 mm

Dimensions of display (W x H) 35 x 28 mm

Height 70.8 mm

Width 141.6 mm

#### Frequency

Frequency range (radio reception) 87.5...108 MHz

#### Measurement

Extension unit input extension unit input for separate on/off switching

#### Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Material Mixed materials

#### Installation, mounting

Installation mode single and combination mounting, screw fastening via supporting plate

#### Connection

Conductor cross-section max. 2.5 mm<sup>2</sup>

Conductor cross-section (loudspeakers)	max. 1.5 mm <sup>2</sup>
Type of connection	with screw terminals
Connection	with 2 loudspeaker connections
<b>Scope of delivery</b>	
Component	with one loudspeaker
<b>Equipment</b>	
Cylinder	8 station memory, non-volatile, switch-on with last station
<b>Use</b>	
Differentiation characteristic 3 - Sales	with loudspeaker
<b>Identification</b>	
Application, usage	Communication technology
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7