



28809909

Radio Touch, with loudspeaker, S.1/B.3/B.7, polar white matt

Technical properties

Functions

Function	volume control ; countdown ; sleep timer ; alarm clock with snooze function
----------	--

Compatibility

For loudspeakers	per channel 4...8 Ω
------------------	---------------------

Controls and indicators

Operation	operation via sensor areas of the touch display
Indication / display	Time and date display ; illuminated touch graphics display

Connectivity

Reception / transmission	stereo FM radio with RDS display
Inputs	external audio input AUX IN

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Insertion depth	33 mm
Dimensions of display (W x H)	35 x 28 mm
Height	70.8 mm
Width	141.6 mm

Frequency

Frequency range (radio reception)	87.5...108 MHz
-----------------------------------	----------------

Measurement

Extension unit input	extension unit input for separate on/off switching
----------------------	--

Materials

Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	matt

Installation, mounting

Installation mode	single and combination mounting ; screw fastening via supporting plate
-------------------	---

Connection

Conductor cross-section	max. 2.5 mm ²
-------------------------	--------------------------

Conductor cross-section (loudspeakers)	max. 1.5 mm ²
Type of connection	with screw terminals
Connection	with 2 loudspeaker connections
Scope of delivery	
Component	with one loudspeaker
Equipment	
Cylinder	8 station memory, non-volatile ; switch-on with last station
Use	
Differentiation characteristic 3 - Sales	with loudspeaker
Identification	
Application, usage	Communication technology
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7