



28809909

## Radio Touch, with loudspeaker, S.1/B.3/B.7, polar white matt

### Technical properties

#### Functions

Function	volume control ; countdown ; sleep timer ; alarm clock with snooze function
----------	--

#### Compatibility

For loudspeakers	per channel 4...8 Ω
------------------	---------------------

#### Controls and indicators

Operation	operation via sensor areas of the touch display
Indication / display	Time and date display ; illuminated touch graphics display

#### Connectivity

Reception / transmission	stereo FM radio with RDS display
Inputs	external audio input AUX IN

#### Dimensions

Insertion depth	33 mm
Dimensions of display (W x H)	35 x 28 mm
Height	70.8 mm
Width	141.6 mm

#### Frequency

Frequency range (radio reception)	87.5...108 MHz
-----------------------------------	----------------

#### Measurement

Extension unit input	extension unit input for separate on/off switching
----------------------	--

#### Materials

Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Mixed materials
Surface appearance	matt

#### Installation, mounting

Installation mode	single and combination mounting ; screw fastening via supporting plate
-------------------	---

#### Connection

Conductor cross-section	max. 2.5 mm <sup>2</sup>
Conductor cross-section (loudspeakers)	max. 1.5 mm <sup>2</sup>

Type of connection	with screw terminals
Connection	with 2 loudspeaker connections
<b>Scope of delivery</b>	
Component	with one loudspeaker
<b>Equipment</b>	
Cylinder	8 station memory, non-volatile ; switch-on with last station
<b>Use</b>	
Differentiation characteristic 3 - Sales	with loudspeaker
<b>Identification</b>	
Application, usage	Communication technology
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7