



28820004

Loudspeaker Arsys stainless steel, lacquered

Technical properties

Configuration

Pre-assembled confectioned, with 2-core, double-insulated, flexible cable

Dimensions

Insertion depth 35 mm

Frequency

Frequency response (-3 dB) 170...18000 Hz

Power

Nominal/music power handling 3/4 W

Resistance

Impedance 4 Ω

Materials

Colour of design line stainless steel

Colour stainless steel

RAL colour RAL 9022 - Pearl light grey

Material / workmanship lacquered

Material Mixed materials

Surface appearance matt

Installation, mounting

Installation mode without spreader claws

Connection

Conductor cross-section (flexible) 0.5 mm²

Cable

Pre-assembled cable 25 cm

Safety

REACH conform Yes

RoHS conform Yes

Identification

Application, usage Communication technology

Main design line Berker Arsys