



28820069

Loudspeaker Arsys, polar white glossy

Technical properties

Configuration

| | |
|---------------|---|
| Pre-assembled | confectioned, with 2-core, double-insulated, flexible cable |
|---------------|---|

Dimensions

| | |
|-----------------|-------|
| Insertion depth | 35 mm |
|-----------------|-------|

Frequency

| | |
|----------------------------|----------------|
| Frequency response (-3 dB) | 170...18000 Hz |
|----------------------------|----------------|

Power

| | |
|------------------------------|-------|
| Nominal/music power handling | 3/4 W |
|------------------------------|-------|

Resistance

| | |
|-----------|------------|
| Impedance | 4 Ω |
|-----------|------------|

Materials

| | |
|-----------------------|-----------------------|
| Colour of design line | polar white |
| Colour | polarwhite |
| RAL colour | RAL 9010 - Pure white |
| Material | Mixed materials |
| Surface appearance | glossy |

Installation, mounting

| | |
|-------------------|------------------------|
| Installation mode | without spreader claws |
|-------------------|------------------------|

Connection

| | |
|------------------------------------|---------------------|
| Conductor cross-section (flexible) | 0.5 mm ² |
|------------------------------------|---------------------|

Cable

| | |
|---------------------|-------|
| Pre-assembled cable | 25 cm |
|---------------------|-------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |

Identification

| | |
|--------------------|--------------------------|
| Application, usage | Communication technology |
| Main design line | Berker Arsys |