



28840004

Radio Touch Arsys stainless steel matt, lacquered

Technical properties

Functions

Function	countdown ; alarm clock with snooze function ; sleep timer ; volume control
----------	---

Compatibility

For loudspeakers	per channel 4...8 Ω
------------------	---------------------

Controls and indicators

Operation	operation via sensor areas of the touch display
Indication / display	Time and date display ; illuminated touch graphics display

Connectivity

Reception / transmission	stereo FM radio with RDS display
Inputs	external audio input AUX IN

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Insertion depth	33 mm
Dimensions of display (W x H)	35 x 28 mm

Frequency

Frequency range (radio reception)	87.5...108 MHz
-----------------------------------	----------------

Measurement

Extension unit input	extension unit input for separate on/off switching
----------------------	--

Materials

Colour of design line	stainless steel
Material / workmanship	lacquered
Surface appearance	matt

Installation, mounting

Installation mode	single and combination mounting ; screw fastening via supporting plate
-------------------	--

Connection

Conductor cross-section	max. 2.5 mm ²
Conductor cross-section (loudspeakers)	max. 1.5 mm ²
Type of connection	with screw terminals
Connection	with 2 loudspeaker connections

Equipment

Cylinder switch-on with last station ; 8 station memory, non-volatile

Identification

Application, usage Communication technology

Main design line Berker Arsys

Instructions

Information text At least one loudspeaker must be connected for operation.