



28840069

Radio Touch Arsys polar white glossy

Technical properties

Functions

Function	countdown ; alarm clock with snooze function ; sleep timer ; volume control
----------	---

Compatibility

For loudspeakers	per channel 4...8 Ω
------------------	---------------------

Controls and indicators

Operation	operation via sensor areas of the touch display
Indication / display	Time and date display ; illuminated touch graphics display

Connectivity

Reception / transmission	stereo FM radio with RDS display
Inputs	external audio input AUX IN

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Insertion depth	33 mm
Dimensions of display (W x H)	35 x 28 mm

Frequency

Frequency range (radio reception)	87.5...108 MHz
-----------------------------------	----------------

Measurement

Extension unit input	extension unit input for separate on/off switching
----------------------	--

Materials

Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Mixed materials
Surface appearance	glossy

Installation, mounting

Installation mode	single and combination mounting ; screw fastening via supporting plate
-------------------	--

Connection

Conductor cross-section	max. 2.5 mm ²
Conductor cross-section (loudspeakers)	max. 1.5 mm ²

Type of connection	with screw terminals
Connection	with 2 loudspeaker connections
Equipment	
Cylinder	switch-on with last station ; 8 station memory, non-volatile
Identification	
Main design line	Berker Arsys
Instructions	
Information text	At least one loudspeaker must be connected for operation.