



28846086

## Radio Touch Q.1/Q.3 anthracite velvety

### Technical properties

#### Functions

Function	countdown, alarm clock with snooze function, sleep timer, volume control
----------	--

#### Compatibility

For loudspeakers	per channel 4...8 Ω
------------------	---------------------

#### Controls and indicators

Operation	operation via sensor areas of the touch display
Indication / display	Time and date display, illuminated touch graphics display

#### Connectivity

Reception / transmission	stereo FM radio with RDS display
Inputs	external audio input AUX IN

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Dimensions

Insertion depth	33 mm
Dimensions of display (W x H)	35 x 28 mm

#### Frequency

Frequency range (radio reception)	87.5...108 MHz
-----------------------------------	----------------

#### Measurement

Extension unit input	extension unit input for separate on/off switching
----------------------	--

#### Materials

Colour of design line	anthracite
Colour	charcoal
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	Mixed materials
Surface appearance	velvety

#### Installation, mounting

Installation mode	single and combination mounting, screw fastening via supporting plate
-------------------	---

#### Connection

Conductor cross-section	max. 2.5 mm <sup>2</sup>
-------------------------	--------------------------

Conductor cross-section (loudspeakers)	max. 1.5 mm <sup>2</sup>
Type of connection	with screw terminals
Connection	with 2 loudspeaker connections
<b>Equipment</b>	
Cylinder	switch-on with last station, 8 station memory, non-volatile
<b>Identification</b>	
Application, usage	Communication technology
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9
<b>Instructions</b>	
Information text	At least one loudspeaker must be connected for operation.