



28846086

## Radio Touch Q.1/Q.3 anthracite velvety

### Technical properties

#### Functions

Function	countdown ; alarm clock with snooze function ; sleep timer ; volume control
----------	---

#### Compatibility

For loudspeakers	per channel 4...8 Ω
------------------	---------------------

#### Controls and indicators

Operation	operation via sensor areas of the touch display
Indication / display	Time and date display ; illuminated touch graphics display

#### Connectivity

Reception / transmission	stereo FM radio with RDS display
Inputs	external audio input AUX IN

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Dimensions

Insertion depth	33 mm
Dimensions of display (W x H)	35 x 28 mm

#### Frequency

Frequency range (radio reception)	87.5...108 MHz
-----------------------------------	----------------

#### Measurement

Extension unit input	extension unit input for separate on/off switching
----------------------	--

#### Materials

Colour of design line	anthracite
Material / workmanship	lacquered
Surface appearance	velvety

#### Installation, mounting

Installation mode	single and combination mounting ; screw fastening via supporting plate
-------------------	--

#### Connection

Conductor cross-section	max. 2.5 mm <sup>2</sup>
Conductor cross-section (loudspeakers)	max. 1.5 mm <sup>2</sup>
Type of connection	with screw terminals
Connection	with 2 loudspeaker connections

---

**Equipment**

Cylinder switch-on with last station ; 8 station memory, non-volatile

---

**Identification**

Application, usage Communication technology

Secondary design line(s) Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

---

**Instructions**

Information text At least one loudspeaker must be connected for operation.