



29512045

LED signal light, RGB, R.1/R.3, black glossy

Technical properties

Architecture

Fixing mode flush-mounting

Main electrical features

Rated voltage 230 V AC

Frequency 50/60 Hz

Power

Power consumption at 195 ... 265 V~, 50/60 Hz - max. 2 W

Materials

Colour of design line black

Colour black

Colour deep black

RAL colour RAL 9005 - Jet black

Material Plastic/metal

Surface appearance glossy

LED control

Quantity LED lamps 4

Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

Connection

Conductor cross-section 2.5 mm²

Settings

Setting Brightness modifiable via potentiometer

Equipment

Lighting Colour sequence can be stopped at any position via the push-button. ; Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button

Switches / socket outlets colour is switchable via an external switch

Use cases

Application Light control

temperatur

Ambient temperature -5...40 °C

Identification

Secondary design line(s)

Berker R.1 ; Berker R.3 ; Serie 1930 ; Series
R.classic**Instructions**

Special note text

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!