



29512045

LED signal light, RGB, R.1/R.3, black glossy

Technical properties

Main electrical features

Rated voltage	230 V AC
Frequency	50/60 Hz

Power

Power consumption	at 195 ... 265 V~, 50/60 Hz - max. 2 W
-------------------	--

Materials

Colour of design line	black
Surface appearance	glossy

LED control

Quantity LED lamps	4
--------------------	---

Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

Connection

Conductor cross-section	2.5 mm ²
-------------------------	---------------------

Settings

Setting	Brightness modifiable via potentiometer
---------	---

Equipment

Lighting	Colour sequence can be stopped at any position via the push-button. ; Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button
Switches / socket outlets	colour is switchable via an external switch

Use cases

Application	Light control
-------------	---------------

temperatur

Ambient temperature	-5...40 °C
---------------------	------------

Identification

Secondary design line(s)	Berker R.1 ; Berker R.3 ; Serie 1930 ; Series R.classic
--------------------------	---

Instructions

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!

Special note text