



29517003

LED signal light, RGB, K.5, al., matt, lacq.

Technical properties

Architecture

Fixing mode flush-mounting

Main electrical features

Rated voltage 230 V AC

Frequency 50/60 Hz

Power

Power consumption at 195 ... 265 V~, 50/60 Hz - max. 2 W

Materials

Colour aluminium

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Material / workmanship lacquered

Material Plastic/metal

Surface appearance matt

LED control

Quantity LED lamps 4

Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

Connection

Conductor cross-section 2.5 mm²

Settings

Setting Brightness modifiable via potentiometer

Equipment

Lighting Colour sequence can be stopped at any position via the push-button., Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button

Switches / socket outlets colour is switchable via an external switch

Use cases

Application Light control

temperatur

Ambient temperature -5...40 °C

Identification

Main design line

Berker K.5

Instructions

Special note text

For consistent illumination of all pilot lamps, connect
max. 5 devices per 10 m of cable length.