



29517003

**LED signal light, RGB, K.5, al., matt, lacq.**

**Technical properties**

**Main electrical features**

Rated voltage	230 V AC
Frequency	50/60 Hz

**Power**

Power consumption	at 195 ... 265 V~, 50/60 Hz - max. 2 W
-------------------	----------------------------------------

**Materials**

Colour of design line	aluminium
Material / workmanship	lacquered
Surface appearance	matt

**LED control**

Quantity LED lamps	4
--------------------	---

**Installation, mounting**

For installation in standard wall boxes	according to DIN 49073-1
-----------------------------------------	--------------------------

**Connection**

Conductor cross-section	2.5 mm <sup>2</sup>
-------------------------	---------------------

**Settings**

Setting	Brightness modifiable via potentiometer
---------	-----------------------------------------

**Equipment**

Lighting	Colour sequence can be stopped at any position via the push-button. ; Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button
Switches / socket outlets	colour is switchable via an external switch

**Use cases**

Application	Light control
-------------	---------------

**temperatur**

Ambient temperature	-5...40 °C
---------------------	------------

**Identification**

Main design line	Berker K.5
------------------	------------

**Instructions**

Special note text	For consistent illumination of all pilot lamps, connect max. 5 devices per 10 m of cable length.
-------------------	--------------------------------------------------------------------------------------------------