



29517006

**LED signal light, RGB, K.1, ant. matt, lacq.**

#### Technical properties

##### Architecture

Fixing mode	flush-mounting
-------------	----------------

##### Main electrical features

Rated voltage	230 V AC
---------------	----------

Frequency	50/60 Hz
-----------	----------

##### Power

Power consumption	at 195 ... 265 V~, 50/60 Hz - max. 2 W
-------------------	--

##### Materials

Colour of design line	anthracite
-----------------------	------------

Colour	charcoal
--------	----------

Colour	anthracite charcoal grey
--------	--------------------------

RAL colour	RAL 7021 - Black grey
------------	-----------------------

Material	Plastic/metal
----------	---------------

Surface appearance	matt
--------------------	------

##### LED control

Quantity LED lamps	4
--------------------	---

##### Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

##### Connection

Conductor cross-section	2.5 mm <sup>2</sup>
-------------------------	---------------------

##### Settings

Setting	Brightness modifiable via potentiometer
---------	---

##### Equipment

Lighting	Colour sequence can be stopped at any position via the push-button., Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button
----------	--

Switches / socket outlets	colour is switchable via an external switch
---------------------------	---

##### Use cases

Application	Light control
-------------	---------------

##### temperatur

Ambient temperature	-5...40 °C
---------------------	------------

<b>Identification</b>	
Main design line	Berker K.1

<b>Instructions</b>	
Special note text	For consistent illumination of all pilot lamps, connect max. 5 devices per 10 m of cable length.