



29521404

LED signal light, red/green lighting, B.7, al., matt, lacq.

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Rated voltage	230 V AC
---------------	----------

Frequency	50/60 Hz
-----------	----------

Power

Power consumption	at 230 V~, 50 Hz - per colour max. 0,5 W
-------------------	--

Materials

Colour	aluminium
--------	-----------

Colour	aluminium optics
--------	------------------

RAL colour	RAL 9006 - White aluminium
------------	----------------------------

Material / workmanship	lacquered
------------------------	-----------

Material	Plastic/metal
----------	---------------

Surface appearance	matt
--------------------	------

LED control

Quantity LED lamps	4
--------------------	---

Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

Connection

Conductor cross-section	2.5 mm ²
-------------------------	---------------------

Equipment

Switches / socket outlets	switchable between red and green via separate switches
---------------------------	--

Use cases

Application	Light control
-------------	---------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

temperatur

Ambient temperature	-5...40 °C
---------------------	------------

Identification	
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7