



29521909

**LED signal light, red/green lighting, S.1/B.3/B.7, p. white, matt, plastic**

**Technical properties**

**Architecture**

Fixing mode flush-mounting

**Main electrical features**

Rated voltage 230 V AC

Frequency 50/60 Hz

**Power**

Power consumption at 230 V~, 50 Hz - per colour max. 0,5 W

**Materials**

Colour of design line polar white

Colour polarwhite

Colour white

RAL colour RAL 9010 - Pure white

Material Plastic/metal

Surface appearance matt

**LED control**

Quantity LED lamps 4

**Installation, mounting**

For installation in standard wall boxes according to DIN 49073-1

**Connection**

Conductor cross-section 2.5 mm<sup>2</sup>

**Equipment**

Switches / socket outlets switchable between red and green via separate switches

**Use cases**

Application Light control

**temperatur**

Ambient temperature -5...40 °C

**Identification**

Main design line Berker S.1/B.3/B.7

Secondary design line(s) Berker S.1, Berker B.3, Berker B.7