



29522089

**LED signal light, red/green lighting, R.1/R.3, p. white glossy**

**Technical properties**

**Main electrical features**

Rated voltage	230 V AC
Frequency	50/60 Hz

**Power**

Power consumption	at 230 V~, 50 Hz - per colour max. 0,5 W
-------------------	--

**Materials**

Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	glossy

**LED control**

Quantity LED lamps	4
--------------------	---

**Installation, mounting**

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

**Connection**

Conductor cross-section	2.5 mm <sup>2</sup>
-------------------------	---------------------

**Equipment**

Switches / socket outlets	switchable between red and green via separate switches
---------------------------	--

**Use cases**

Application	Light control
-------------	---------------

**Safety**

REACH conform	Yes
RoHS conform	Yes

**temperatur**

Ambient temperature	-5...40 °C
---------------------	------------

**Identification**

Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	KNX ; Berker R.1 ; Berker R.3 ; Serie 1930 ; Series R.classic

**Instructions**

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!

Special note text