



29522089

LED signal light, red/green lighting, R.1/R.3, p. white glossy

Technical properties

Main electrical features

| | |
|---------------|----------|
| Rated voltage | 230 V AC |
| Frequency | 50/60 Hz |

Power

| | |
|-------------------|--|
| Power consumption | at 230 V~, 50 Hz - per colour max. 0,5 W |
|-------------------|--|

Materials

| | |
|-----------------------|-----------------------|
| Colour of design line | polar white |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Surface appearance | glossy |

LED control

| | |
|--------------------|---|
| Quantity LED lamps | 4 |
|--------------------|---|

Installation, mounting

| | |
|---|--------------------------|
| For installation in standard wall boxes | according to DIN 49073-1 |
|---|--------------------------|

Connection

| | |
|-------------------------|---------------------|
| Conductor cross-section | 2.5 mm ² |
|-------------------------|---------------------|

Equipment

| | |
|---------------------------|--|
| Switches / socket outlets | switchable between red and green via separate switches |
|---------------------------|--|

Use cases

| | |
|-------------|---------------|
| Application | Light control |
|-------------|---------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |

temperatur

| | |
|---------------------|------------|
| Ambient temperature | -5...40 °C |
|---------------------|------------|

Identification

| | |
|--------------------------|---|
| Main design line | Berker R.1/R.3/R.8 |
| Secondary design line(s) | KNX ; Berker R.1 ; Berker R.3 ; Serie 1930 ; Series R.classic |

Instructions

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!

Special note text