



29527003

**LED signal light, red/green lighting, K.5, al., matt, lacq.**

#### Technical properties

##### Architecture

Fixing mode	flush-mounting
-------------	----------------

##### Main electrical features

Rated voltage	230 V AC
---------------	----------

Frequency	50/60 Hz
-----------	----------

##### Power

Power consumption	at 230 V~, 50 Hz - per colour max. 0,5 W
-------------------	--

##### Materials

Colour	aluminium
--------	-----------

Colour	aluminium optics
--------	------------------

RAL colour	RAL 9006 - White aluminium
------------	----------------------------

Material / workmanship	lacquered
------------------------	-----------

Material	Plastic/metal
----------	---------------

Surface appearance	matt
--------------------	------

##### LED control

Quantity LED lamps	4
--------------------	---

##### Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

##### Connection

Conductor cross-section	2.5 mm <sup>2</sup>
-------------------------	---------------------

##### Equipment

Switches / socket outlets	switchable between red and green via separate switches
---------------------------	--

##### Use cases

Application	Light control
-------------	---------------

##### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

##### temperatur

Ambient temperature	-5...40 °C
---------------------	------------

