



29527004

**LED signal light, red/green lighting, K.5, stainless steel matt, lacq.**

**Technical properties**

**Architecture**

Fixing mode flush-mounting

**Main electrical features**

Rated voltage 230 V AC

Frequency 50/60 Hz

**Power**

Power consumption at 230 V~, 50 Hz - per colour max. 0,5 W

**Materials**

Colour of design line stainless steel

Colour Stainless steel

Colour stainless steel optics

RAL colour RAL 9022 - Pearl light grey

Material / workmanship lacquered

Material Plastic/metal

Surface appearance matt

**LED control**

Quantity LED lamps 4

**Installation, mounting**

For installation in standard wall boxes according to DIN 49073-1

**Connection**

Conductor cross-section 2.5 mm<sup>2</sup>

**Equipment**

Switches / socket outlets switchable between red and green via separate switches

**Use cases**

Application Light control

**temperatur**

Ambient temperature -5...40 °C

**Identification**

Main design line Berker K.5