



29531404

**LED signal light, white lighting, B.7, al., matt, lacq.**

#### Technical properties

##### Architecture

Fixing mode flush-mounting

##### Main electrical features

Rated voltage 230 V AC

Frequency 50/60 Hz

##### Power

Power consumption at 230 V~, 50 Hz - max. 1 W

##### Materials

Colour aluminium

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Material / workmanship lacquered

Material Plastic/metal

Surface appearance matt

##### LED control

Quantity LED lamps 4

##### Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

##### Connection

Conductor cross-section 2.5 mm<sup>2</sup>

##### Settings

Setting Brightness modifiable via potentiometer

##### Equipment

Lighting Light colour cold white

Switches / socket outlets switchable via separate switch

##### Use cases

Application Light control

##### temperatur

Ambient temperature -5...40 °C

##### Identification

Main design line Berker S.1/B.3/B.7

