



29531909

LED signal light, white lighting, S.1/B.3/B.7, p. white, matt, plastic

Technical properties

Architecture

Fixing mode flush-mounting

Main electrical features

Rated voltage 230 V AC

Frequency 50/60 Hz

Power

Power consumption at 230 V~, 50 Hz - max. 1 W

Materials

Colour of design line polar white

Colour polarwhite

Colour white

RAL colour RAL 9010 - Pure white

Material Plastic/metal

Surface appearance matt

LED control

Quantity LED lamps 4

Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

Connection

Conductor cross-section 2.5 mm²

Settings

Setting Brightness modifiable via potentiometer

Equipment

Lighting Light colour cold white

Switches / socket outlets switchable via separate switch

Use cases

Application Light control

temperatur

Ambient temperature -5...40 °C

Identification

Main design line Berker S.1/B.3/B.7

