



29532045

**LED signal light, white lighting, R.1/R.3, black glossy**

**Technical properties**

**Architecture**

Fixing mode flush-mounting

**Main electrical features**

Rated voltage 230 V AC

Frequency 50/60 Hz

**Power**

Power consumption at 230 V~, 50 Hz - max. 1 W

**Materials**

Colour of design line black

Colour black

Colour deep black

RAL colour RAL 9005 - Jet black

Material Plastic/metal

**LED control**

Quantity LED lamps 4

**Installation, mounting**

For installation in standard wall boxes according to DIN 49073-1

**Connection**

Conductor cross-section 2.5 mm<sup>2</sup>

**Settings**

Setting Brightness modifiable via potentiometer

**Equipment**

Lighting Light colour cold white

Switches / socket outlets switchable via separate switch

**Use cases**

Application Light control

**Safety**

Protection index IP IP20

**temperatur**

Ambient temperature -5...40 °C

---

**Identification**

Main design line

Berker R.1/R.3/R.8

Secondary design line(s)

Berker R.1, Berker R.3, Serie 1930, Series R.classic

---

**Instructions**

Special note text

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!