



29532089

LED signal light, white lighting, R.1/R.3, p. white glossy

Technical properties

Architecture

Fixing mode flush-mounting

Main electrical features

Rated voltage 230 V AC

Frequency 50/60 Hz

Power

Power consumption at 230 V~, 50 Hz - max. 1 W

Materials

Colour of design line polar white

Colour polarwhite

Colour white

RAL colour RAL 9010 - Pure white

Material Plastic/metal

LED control

Quantity LED lamps 4

Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

Connection

Conductor cross-section 2.5 mm²

Settings

Setting Brightness modifiable via potentiometer

Equipment

Lighting Light colour cold white

Switches / socket outlets switchable via separate switch

Use cases

Application Light control

Safety

Protection index IP IP20

temperatur

Ambient temperature -5...40 °C

Identification

Main design line

Berker R.1/R.3/R.8

Secondary design line(s)

Berker R.1, Berker R.3, Serie 1930, Series R.classic

Instructions

Special note text

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!