



3031

## Rocker switch off, Module inserts

### Technical properties

#### Architecture

Type of control unit	single rocker
Fixing mode	flush-mounting

#### Configuration

Switch mode	Off
Antibacterial treatment	No

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Controls and indicators

Push-buttons	No
--------------	----

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

#### Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

#### Dimensions

Depth	41.6 mm
Insertion depth	31 mm
Height	70.8 mm
Width	70.8 mm

#### Materials

Material	Plastic/metal
Surface appearance	other

#### Installation, mounting

Installation mode	with spreader claws, for screw fastening
-------------------	--

#### Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with plug-in terminals
Type of connection	Quickconnect

**Equipment**

---

Lighting	for lighting and monitoring circuit
Heating switch	No

---

**Use cases**

---

Application	Light control
-------------	---------------

---

**Safety**

---

Protection index IP	IP20
Impact strength	IK07

---

**Identification**

---

Application, usage	Light control
Main design line	Light control

---