



3031

Rocker switch off, Module inserts

Technical properties

Architecture

Type of control unit	single rocker
Fixing mode	flush-mounting

Configuration

Switch mode	Off
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	41.6 mm
Insertion depth	31 mm
Height	70.8 mm
Width	70.8 mm

Materials

Material	Plastic/metal
Surface appearance	other

Installation, mounting

Installation mode	with spreader claws, for screw fastening
-------------------	--

Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with plug-in terminals
Type of connection	Quickconnect

Equipment	
Lighting	for lighting and monitoring circuit
Heating switch	No
Use cases	
Application	Light control
Safety	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07
Identification	
Application, usage	Light control
Main design line	Light control