



303303

On/off switch 3pole 16AX/400V

Technical properties

Architecture

Type of control unit single rocker

Configuration

Switch mode 3-pole off ; with predefined neutral position

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 400 V

Rated voltage 400 V AC

Electric current

Switching current 16 A

Dimensions

Depth 42 mm

Insertion depth 31 mm

Height 71 mm

Width 71 mm

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Lighting for lighting and monitoring circuit

Heating switch No

Use cases

Application Light control

Safety

Impact strength

IK07

Identification

Application, usage

HVAC control ; Light control

Main design line

Light control

Instructions

Information text

spreader claws, insulated to the supporting ring, self-resetting ; Only suitable in combination with rockers with "0" imprint.