



303650

**Change-over switch for inst. in hollow walls, light control**

**Technical properties**

**Architecture**

Type of control unit single rocker

**Functions**

Switching angle 3.5 °

**Configuration**

Switch mode Off/change-over

Antibacterial treatment No

**Compatibility**

IFTTT support available No

**Controls and indicators**

Push-buttons No

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

**Electric current**

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

**Dimensions**

Depth 41.6 mm

Insertion depth 19.5 mm

Height 71 mm

Width 71 mm

**Materials**

Surface appearance matt

**Installation, mounting**

Installation mode without spreader claws ; low installation depth ; for screw fastening

**Connection**

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

**Equipment**

---

Lighting	for lighting and monitoring circuit
Heating switch	No

---

**Use cases**

---

Application	Barrier-free application ; HVAC-control ; Light control
-------------	---

---

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

---

**Identification**

---

Application, usage	Light control ; HVAC control
Main design line	Light control

---