



303650

Change-over switch for inst. in hollow walls, light control

Technical properties

Architecture

Type of control unit single rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode Off/change-over

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 41.6 mm

Insertion depth 19.5 mm

Height 71 mm

Width 71 mm

Materials

Surface appearance matt

Installation, mounting

Installation mode without spreader claws ; low installation depth ; for screw fastening

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

Equipment

Lighting	for lighting and monitoring circuit
Heating switch	No

Use cases

Application	Barrier-free application ; HVAC-control ; Light control
-------------	---

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Identification

Application, usage	Light control ; HVAC control
Main design line	Light control
