



3315327004

3 x Cinch/S-Video soc. out., K.5, stainless steel matt, lacq.

Technical properties

Connectivity

Outlet	with straight outlet
Connectors / jacks	2 cinch double jacks for audio connection (red, white), S-Video double jack, 1 cinch double jack for video connection (yellow)

Frequency

Frequency range audio	20 Hz...20 kHz
Frequency range video	max. 160 MHz

Materials

Colour of design line	stainless steel
Colour	stainless steel
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	lacquered
Material	Plastic/metal
Surface appearance	matt
Material / surface	gold-plated contacts

Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

Equipment

Supporting plate / Supporting ring	with supporting ring
------------------------------------	----------------------

Identification

Application, usage	Communication technology
Main design line	Berker K.5

Instructions

Information text	Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; for connecting analogue audio and video devices such as receivers, hi-fi systems and DVD players. ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092
------------------	---