



3315396084

**USB/3.5 mm audio socket outlet, Q.1/Q.3, aluminium velvety, lacquered**

**Technical properties**

**Connectivity**

Outlet	with straight outlet
Connectors / jacks	USB, double socket type A, USB 2.0 compliant, double jack gold-plated 3.5 mm, stereo

**Dimensions**

Insertion depth	24.9 mm
-----------------	---------

**Frequency**

Frequency range audio	20 Hz...20 kHz
-----------------------	----------------

**Storage**

USB transmission rate	max. 480 Mbit/s
-----------------------	-----------------

**Materials**

Colour	aluminium
RAL colour	RAL 9006 - White aluminium
Material	Plastic/metal
Surface appearance	velvety

**Installation, mounting**

Installation mode	without spreader claws
-------------------	------------------------

**Identification**

Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9
--------------------------	--

**Instructions**

Information text	<p>Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For connecting mobile devices, such as mobile phones or MP3 players (mini audio), digital cameras and computer peripherals (USB 2.0). ; Observe the instructions of the cable and device manufacturers for maximum USB cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092</p>
------------------	--