



3315397006

**USB/3.5 mm audio soc. out., K.1, ant. matt, lacq.**

#### Technical properties

##### Connectivity

Outlet	with straight outlet
Connectors / jacks	USB, double socket type A, USB 2.0 compliant ; double jack gold-plated 3.5 mm, stereo

##### Dimensions

Insertion depth	24.9 mm
-----------------	---------

##### Frequency

Frequency range audio	20 Hz...20 kHz
-----------------------	----------------

##### Storage

USB transmission rate	max. 480 Mbit/s
-----------------------	-----------------

##### Materials

Colour of design line	anthracite
Material / workmanship	lacquered
Surface appearance	matt

##### Installation, mounting

Installation mode	without spreader claws ; for screw fastening
-------------------	----------------------------------------------

##### Identification

Application, usage	Communication technology
Main design line	Berker K.1

##### Instructions

Information text	Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For connecting mobile devices, such as mobile phones or MP3 players (mini audio), digital cameras and computer peripherals (USB 2.0). ; Observe the instructions of the cable and device manufacturers for maximum USB cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092
------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------