



3315408982

## VGA soc. out., S.1, white glossy

### Technical properties

#### Connectivity

Outlet	with straight outlet
Plug type	S-VGA compatible
Connectors / jacks	with 15pole D-subminiature jack (front)

#### Dimensions

Insertion depth	12 mm
-----------------	-------

#### Frequency

Frequency range video	max. 160 MHz
-----------------------	--------------

#### Screen

Resolution	max. 1280 x 1024 px
------------	---------------------

#### Materials

Colour of design line	white
Colour	white
Surface appearance	glossy

#### Installation, mounting

Installation mode	without spreader claws ; for screw fastening
-------------------	--

#### Connection

Type of connection	with backside jack for connecting to pre-assembled VGA cable
Connection	with 15pole D-subminiature double jack

#### Equipment

Supporting plate / Supporting ring	with supporting ring
------------------------------------	----------------------

#### Safety

REACH conform	Yes
RoHS conform	Yes

#### Identification

Application, usage	Communication technology
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7

#### Instructions

Information text

For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74