



3315417006

VGA soc. out., screw-in lift terminals, K.1, ant. matt, lacq.

Technical properties

Connectivity

Outlet	with straight outlet
Plug type	S-VGA compatible
Connectors / jacks	with 15pole D-subminiature jack (front)

Frequency

Frequency range video	max. 160 MHz
-----------------------	--------------

Screen

Resolution	max. 1280 x 1024 px
------------	---------------------

Materials

Colour of design line	anthracite
Material / workmanship	lacquered
Surface appearance	matt

Installation, mounting

Installation mode	without spreader claws ; for screw fastening
-------------------	--

Connection

Conductor cross-section	max. 1.5 mm ²
Type of connection	with screw-in lift terminals for connection to 15-core VGA cable

Equipment

Supporting plate / Supporting ring	with supporting ring
------------------------------------	----------------------

Use

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

Safety

REACH conform	Yes
RoHS conform	Yes

Identification

Application, usage	Communication technology
Main design line	Berker K.1

Instructions

Information text

For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74