



3315417006

**VGA soc. out., screw-in lift terminals, K.1, ant. matt, lacq.**

#### Technical properties

##### Connectivity

Outlet	with straight outlet
Plug type	S-VGA compatible
Connectors / jacks	with 15pole D-subminiature jack (front)

##### Frequency

Frequency range video	max. 160 MHz
-----------------------	--------------

##### Screen

Resolution	max. 1280 x 1024 px
------------	---------------------

##### Materials

Colour of design line	anthracite
Colour	anthracite
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	Plastic/metal
Surface appearance	matt

##### Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

##### Connection

Conductor cross-section	max. 1.5 mm <sup>2</sup>
Type of connection	with screw-in lift terminals for connection to 15-core VGA cable

##### Equipment

Supporting plate / Supporting ring	with supporting ring
------------------------------------	----------------------

##### Use

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

##### Identification

Application, usage	Communication technology
Main design line	Berker K.1

##### Instructions

Information text

For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74