



3315418989

VGA soc. out., screw-in lift terminals, S.1/B.3/B.7, p. white glossy

Technical properties

Connectivity

Outlet	with straight outlet
Plug type	S-VGA compatible
Connectors / jacks	with 15pole D-subminiature jack (front)

Frequency

Frequency range video	max. 160 MHz
-----------------------	--------------

Screen

Resolution	max. 1280 x 1024 px
------------	---------------------

Materials

Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Surface appearance	glossy

Installation, mounting

Installation mode	without spreader claws ; for screw fastening
-------------------	--

Connection

Conductor cross-section	max. 1.5 mm ²
Type of connection	with screw-in lift terminals for connection to 15-core VGA cable

Equipment

Supporting plate / Supporting ring	with supporting ring
------------------------------------	----------------------

Use

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

Safety

REACH conform	Yes
RoHS conform	Yes

Identification

Application, usage	Communication technology
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7

Instructions

Information text

For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74